

DECLARATION OF COMPLIANCE Ultipleat® High Flow Filter Elements CAS Series “W” Code

Element Part Number

HFU 6 CAS010 J U W
Table 1

This is a guide to the part numbering structure only. For specific options, please contact Pall.

Table 1 : Nominal Length


Code	Description
20	508 mm (20")
40	1016 mm (40")
60	1524 mm (60")

The Ultipleat CAS High Flow Filter element is a large diameter, disposable, pleated, filter cartridge for high flow rates in water, with an inside-to-outside flow pattern.

The filter is intended for use in food and beverage water filtration applications at up to 50 °C (122 °F).

An initial flush is recommended prior to use.

Issued 1 May 2010
Revised 07 January 2015
Expires 28 February 2017
Reference FBDCCASENg
Page 1 of 3



James LeRoy
Director of Quality
Pall Cortland

Ultipleat High Flow Filter Elements (CAS Series "W" Code)

Components

Filter Media	Pall proprietary Supor [®] polyethersulfone membrane and proprietary melt blown polypropylene Profile [®] UP media
Support Mesh and Outer Wrap	Polypropylene
Wrap Adhesive	Hot air bonding
End Caps and Handle	White (TiO ₂ filled) colored polypropylene moldings (10 % glass reinforced)
Seal	Ethylene Propylene Rubber (JUW option)

Declaration

Ultipleat High Flow CAS Series filter elements comprise materials that meet regulatory and legislative requirements and guidelines for food contact in that:

Europe

The "W" Code Ultipleat CAS High Flow Filter Elements meet the requirements for aqueous food contact as detailed in European Regulation (EC) Number 1935/2004 in that:

- Our suppliers' information indicates that the plastic components employed are made from monomers and additives consistent with Annex I of Commission Regulation (EU) Number 10/2011 and its amendments, relating to plastic materials and articles intended to come into contact with foodstuffs.

Overall Migration Limit testing of HFU hardware components and support mesh has been performed after flushing and in flow conditions (excluding seals) in:

Simulant A (10% ethanol) at 100 °C (212 °F) for 4 hours
 Simulant B (3% acetic acid) at 100 °C (212 °F) for 4 hours
 Distilled water at 100°C (212 °F) for 4 hours

SML testing of support mesh material has been performed after flushing and in flow conditions in:

Simulant A (10% ethanol) at 100 °C (212 °F) for 4 hours
 Simulant B (3% acetic acid) at 100 °C (212 °F) for 4 hours
 Distilled water at 100 °C (212 °F) for 4 hours

SML testing of CAS010 filter pack has been conducted after flushing and in flow conditions, in:

Distilled water at 50 °C (122 °F) for 2 hours.

Note:

This product contains materials that are subject to SML requirements.

This product contains calcium stearate, which is approved as a direct food additive.

- Glass fibers are approved as an additive to plastic within Regulation 10/2011 under reference number 55520.

USA

The thermoplastic filter components, with the exception of the glass-filler in the molded end caps, meet the FDA requirements for food contact use as detailed in Code of Federal Regulations, 21CFR paragraphs 170-199 in that:

- The molded end caps utilize glass filler to enhance strength and maintain dimensional stability. The fibers are considered encapsulated by the endcap base resin.
- Polypropylene to 21CFR section 177.1520 (Olefin polymers) and section 178.2010 (antioxidants and/or stabilizers or polymers).
- Typical Supor membranes were analyzed as per ASTM test methods for conformance to FDA specifications for food contact substances. The membranes met the specifications for polyethersulfone resins as described in Title 21 of the U.S. Code of Federal Regulations 177.2440, paragraphs (a), (b) and (c) including acceptable heavy metal content. Additionally, no specified or known adjuvants were detected at a limit of 0.001%.
- Ethylene Propylene Rubber seal material to 21CFR section 177.2600 (Rubber articles intended for repeated use, excluding milk and edible oils)

Process Quality System

Site of Manufacture: Pall Cortland, USA.

The Quality Management System at Pall Cortland is certified to ISO 9001:2008.

These products / product packaging carry a lot number / date code to facilitate traceability to suppliers' materials and Pall production records.

Supplied in Europe by

Pall International Sàrl
Av. de Tivoli 3
Fribourg
Switzerland
CH-1700




Pall Food and Beverage

New York - USA
+1 516 484 3600 telephone
+1 866 905 7255 toll free
foodandbeverage@pall.com

Visit us on the web at www.pall.com

Pall Corporation has offices throughout the world. For Pall representatives in your area, please go to www.pall.com/contact.

Because of developments related to products, systems and/or services described herein, the data and procedures are subject to change without notice. Please consult your Pall representative or visit www.pall.com to verify that this information remains valid.

© Copyright 2015, Pall Corporation. Pall, , Profile, Supor and Ultipleat are trademarks of Pall Corporation. ® indicates a trademark registered in the USA. Filtration.Separation.Solution is a service mark of Pall Corporation.